

Product Name :
Magnetic Separator

Product Code :
NLAB-TECHNICALAB31010



Description :

Magnetic Separator

Technical Specification :

Materials, that have different magnetic at tractability, may be separated by passing them through a magnetic field. Most often, magnetic separation techniques are used to remove iron, steel or magnetic iron oxide from materials low in magnetic at tractability. These devices operate in either a continuous or a cyclic manner. Continuous devices usually have a belt which moves over the lifting magnetic poles to carry the magnetize partials into a region of low or zero magnetic field, where they are released. The present set-up is of In-line lifting magnet type.

The set-up consists of two belts moving separately in opposite direction at slow speed. Feed through a vibrating hopper is conveyed over first belt and allowed to pass near the second belt, which is under magnetic field. The magnetic field is generated by permanent magnet kept in a box. Magnetically inert material drops off the belt in a normal manner. Magnetic material is held on the belt, however, and finally drops off the belt as it leaves the magnetic field. Both the belts are fitted on the pulleys and driven by an electric motor coupled with a reduction gearbox.

Experimentation:

To study the Principles and operation of a Magnetic Separator.

To determine the efficiency of Magnetic Separator.

Utilities Required :

Raw Material for Feed.

Electric Supply : Single phase, 220 V AC, 1 kW.

Floor Area 1.5 m x 1 m.

Weighing Balance

Technical Details :

Belts: Width 150mm, Length 500mm

Feed Hopper: Material Stainless Steel, Suitable capacity (Continuously Vibrating)

Drive: FHP motor with Reduction Gear Box.

Magnets: Permanent Magnets kept in a Stainless Steel chamber.

Collecting Bin: 2 Nos. One each for Magnetic and Non-Magnetic material.

Naugralabequipments

Website: www.naugralabequipments.com, **Email:** sales@naugralabequipments.com

Address: 6148/6, Guru Nanak Marg, Ambala Cantt, Haryana, India. **Phone:** +91-9896600003